






NOTE:

- 1 .ELECTRICAL CHARACTERISTICS
 - 1-1 RATING CURRENT: 3A AC/DC
 - 1-2 RATING VOLTAGE: 250V AC/DC
 - 1-3 INSULATION RESISTANCE: 1000M OHMS MIN
 - 1-4 WITHSTANDING VOLTAGE: 800V AC/1MINUTE
 - 1-5 OPERATING TEMPERATURE: -40°C~+105°C
- 2. MATERIAL:
 - PA66, UL 94V-0, NATURAL COLOR
- 3. USED WITH AFCI 10156617
- 4. PRODUCT SPEC: GS-12-1595
- 5. ORDERING CODE: 10156616-XX 0 X LF

NUMBER OF PINS PACKAGE
 02~16: 02~16PINS 0: BAG



POS	DIMENSIONS(MM)		POS	DIMENSIONS(MM)	
	A	B		A	B
2	2.50	6.50	10	22.50	26.50
3	5.00	9.00	11	25.00	29.00
4	7.50	11.50	12	27.50	31.50
5	10.00	14.00	13	30.00	34.00
6	12.50	16.50	14	32.50	36.50
7	15.00	19.00	15	35.00	39.00
8	17.50	21.50	16	37.50	41.50
9	20.00	24.00			



mat'l. code		surface ISO 1302	tolerance ISO 406 ISO 101	projection	product family
ltr		ecn no	dr	date	MINITEK
A		New release	Jason	2020-2-19	title
		angles	linear	.X±.3	2.5PITCH BOARD-IN, R/A , HOUSING
		0°±x'		.XX±.20	dwg no
				.XXX±.10	sheet 1 of 1
		dr	Jason Wang	2020-2-19	size
		enr	Jason Wang	2020-2-19	10156616
		chr	-	-	A3
		appd	Tim Yao	2020-2-19	type
					Product Customer Drawing
sheet index	revision sheet	A	1		

Amphenol FCI

© 2016 AFCI