7-1768042-2 - ACTIVE

Agastat 7000 TE Internal #: 7-1768042-2 Pre-Printed Markers, Snap-On, STD 03 Marker Size, Yellow, Straight Cut, Y Printed Marking, Black, Polyoxymethylene, Agastat 7000 View on TE.com >



Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: Snap-On Marker Size: STD 03 Compatible Cable Diameter Range: 1.9 – 2.6 mm [.075 – .102 in] Primary Product Color: Yellow Marker Cut: Straight

All STD Snap-On Markers (966)

Features

Body Features

Marker Style

Marker Size

Snap-On

STD 03

Marker Size	STD 03
Primary Product Color	Yellow
Primary Product Material	Polyoxymethylene
Dimensions	
Compatible Cable Diameter Range	1.9 – 2.6 mm[.075 – .102 in]
Printer/Label Features	
Marker Cut	Straight
Printed Marking	Y
Packaging Features	
Packaging Method	Strip
Packaging Quantity	300
Other	
Printed Marking Color	Black
Product Compliance	
For compliance documentation, visit the product page on TE.com>	

7-1768042-2

Pre-Printed Markers, Snap-On, STD 03 Marker Size, Yellow, Straight Cut, Y Printed Marking, Black, Polyoxymethylene, Agastat 7000



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




Also in the Series | Agastat 7000


7-1768042-2

Pre-Printed Markers, Snap-On, STD 03 Marker Size, Yellow, Straight Cut, Y Printed Marking, Black, Polyoxymethylene, Agastat 7000





Customers Also Bought



Documents

Product Drawings STD03Y-Y English

Datasheets & Catalog Pages

STD/STB-type Snap-on Pre-printed Wire & Cable Markers

English

IDENTIFICATION SELECTION GUIDE

English

STD and STB Technical Datasheet

English

Product Specifications RW-2538 STD and STB work instruction

English