

# RNF-100-3/32-0-SP ✓ ACTIVE

RAYCHEM | RAYCHEM RNF-100

TE Internal #: 5052944058

Heat Shrink Tubing, Black, Single Wall, .093 in [2.4 mm] Expanded Inside, .046 in [1.2 mm] Recovered Inside, 2:1 Shrink Ratio, RAYCHEM RNF-100

[View on TE.com >](#)



Heat Shrink Tubing > RNF-3000 Single Wall Stick Heat Shrink



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **2.4 mm [ .093 in ]**

Recovered Inside Diameter (Max): **1.2 mm [ .046 in ]**

Shrink Ratio: **2:1**

[All RNF-3000 Single Wall Stick Heat Shrink \(178\)](#)

## Features

### Product Type Features

Product Family	RNF-100
Wall Type	Single

### Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

### Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

### Dimensions

Recovered Wall Thickness (Tolerance)	.2 mm[.008 in]
Recovered Wall Thickness (Nominal)	.5 mm[.02 in]
Expanded Inside Diameter (Min)	2.4 mm[.093 in]
Recovered Inside Diameter (Max)	1.2 mm[.046 in]
Heat Shrink Tubing Size Range	1.2 – 2.4 mm[.046 – .093 in]



### Usage Conditions

Shrink Temperature (Min)	95 °C
Fluid Resistance	Splash Protection
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
Recovery Temperature	121 °C

### Product Availability

Applicable Region	Global
-------------------	--------

### Packaging Features

Packaging Method	Box
------------------	-----

### Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Also in the Series | RAYCHEM RNF-100



Heat Shrink Tubing(985)



Power Cable Tubing & Accessories(8)

## Customers Also Bought




TE Part #5053114035  
RNF-3000 Single Wall Stick Heat Shrink




TE Part #5053094080  
RNF-100-1/4-0-SP




TE Part #CV21254001  
RW-175-E-1/16-X-SP



TE Part #4-2176453-1  
CPF 0201 15K 0.1% 25ppm 1K RL



TE Part #5-2176453-7  
CPF 0201 22K1 0.1% 25ppm 1K RL




TE Part #9-2176452-2  
CPF 0201 4K75 0.1% 25ppm 1K RL



TE Part #NB16544001  
RW-175-3/32-0-SP



TE Part #CV31202001  
RW-175-E-1/16-X-STK-CS34070



TE Part #NB-PTCO-017  
PTFC102S1N5:ASSEMBLY,S

## Documents

[Product Drawings](#)  
[RNF-100-3/32-0-SP](#)



English

---

**Datasheets & Catalog Pages**

**RNF-100 Pages from 9-1773447-9**

English

---

**Product Specifications**

**Quality Specification**

English

---

**Product Environmental Compliance**

**Safety Datasheet**

English

**Safety Datasheet**

English

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

English

**Safety Datasheet**

French

**Safety Datasheet**

German

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

**Safety Datasheet**

English

**Safety Datasheet**