■ NEWS & EVENTS ▼

H ABOUT US ▼



Products > Switches > Pressure Switches > Standard Pressure Switches > 5000 Series > 76079

#### Overview

Honeywell

5000 Series pressure switch with standard terminal. These switches sense a change in the pressure, opening or closing an electrical circuit when the designated set point is reached. Honeywell S&C offers an impressive line of standard products, but our engineering expertise and understanding afford us the ability to modify existing parts or create an original component per a customer's specifications.



view distributor inventory

? sample request

email technical support













find a distributor

# **Technical Specifications**

Operating Pressure	250 psi	
Connector(s)	1/8-27 NPT	
Standard Factory Set Points	60 psi	
Circuitry	NO/NC, adjustable	
Proof Pressure	500 psi	

Product Type	Switch
Contact Setting Range	51 psi to 90 psi, ±7 psi
Electrical Termination	1/4 in spade terminals
Contact(s)	Silver alloy, gold plated
Burst Pressure	1250 psi

View documents in: English

View More

#### **Documents**

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
HP, HE, MH, ME, LP, and LE Series Pressure Switches Datasheet	Datasheet	English	3МВ
Series 5000 Extended Duty Pressure Switch Datasheet	Datasheet	English	120KB
Embedded Products in Hospital Applications	Brochure	English	5MB
HP-HE-ME-LP-LE Series Applications	Application Note	English	1MB

View More

### **Product Features**

- Stands up to extended duty applications
- · Factory set, capable of field adjustment
- Direct acting blade gold-plated contacts
- No dead band
- Kapton diaphragm for compatibility with a variety of fluids
- Various electrical connections and terminations
- · Optional rubber boot

## **Applications**

- Engine transmission
- Hydraulics and brakes
- Power steering
- Fuel pressure
- ABS brakes
- Cruise control
- Oxygen concentrators
- Dental air
- Embalming equipment
- Generators/compressors
- Pool/spa water pressure

NAVIGATION LINKS DISTRIBUTOR LINKS

HOME PAGE ECOM LOGIN

PRODUCTS LEARN CENTER

DISTRIBUTOR INVENTORY REQUEST ACCESS TO ECOM

INDUSTRIES SALES/AD PORTAL LOGIN

SUPPORT SALES/AD PORTAL ACCESS REQUEST

NEWS & EVENTS SAMPLE REQUEST

ABOUT US SUPPLIER MICROSITE

LANGUAGE

English 🔻

SOCIAL MEDIA



SITE INFORMATION

PRIVACY STATEMENT

SITE MAP

TERMS & CONDITIONS

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please set Don't show this message again