

WW1A24A-D8

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Basic Switches](#) : [MICRO SWITCH™ Special Application Precision Switches](#) : [WW](#))



WW Series Snap-in Panel Mount Switch, Single Pole Normally Closed (SPNC) Circuitry, 3 A at 125 Vac, Plunger Lever, Quick Connect Termination

Actual product appearance may vary.

Product Specifications

Switch Type	Snap-in Panel Mount (13,97 mm x 28,45 mm [0.55 in x 1.12 in] panel cutout)
Sealed	No
Ampere Rating	3 A
Circuitry	SPNC
Actuator	Plunger Lever
Termination	Quick Connect
Voltage	125 Vac
Actuator Length	12,5 mm [.49 in]
Overtravel (OT)	5,0 mm [0.20 in] min.
Operating Position (OP)	3,5 mm [0.14 in]
Material	Plastic
Housing Material	Plastic
Expected Mechanical Life	100000 cycles
Agency Approvals and Standards	UL, CSA
Package Height	40,00 mm [1.575 in]
Package Width	31,52 mm [1.241 in]
Package Length	17,53 mm [0.69 in]
Recommended For	Door Status Indication
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap switches
Series Name	WW