



TE Internal #: 2267130-3

Push Button Switches, Single Pole - Single Throw Configuration (Pole-Throw), Switch, Single Actuator, Extended Actuator Profile, Unthreaded

[View on TE.com >](#)

Relays, Contactors & Switches > Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Switch**

Number of Actuators: **Single**

Actuator Profile: **Extended**

Bushing Style: **Unthreaded**

Features

Product Type Features

Dust Proof	Yes
Push Button Switch Product Type	Switch
Illuminated	No
Actuator Style	Round

Configuration Features

ESD Grounding Terminal	Without
Ganged	No
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	Off [On]

Electrical Characteristics

--	--



Push Button Switch Voltage Rating	20 VDC
-----------------------------------	--------

Body Features

Seal Type	Internal Actuator O-Ring
Case Material	Nylon 4/6
Actuator Material	Thermoplastic Polyester
Actuator Profile	Extended
Bushing Style	Unthreaded
Actuator Color	White

Contact Features

Contact Base Material	Copper Alloy
Push Button Switch Contact Current Rating	.4 A
Switch Contact Plating Material	Gold

Termination Features

Termination Type	Printed Circuit
------------------	-----------------

Mechanical Attachment

Mounting Angle	Right Angle
Push Button Switch Mounting Type	Surface Mount

Housing Features

Low Profile	Yes
Process Sealed	Yes

Dimensions

Actuator Length	5.6 mm[.22 in]
-----------------	----------------

Usage Conditions

Temperature Rating	Standard
--------------------	----------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Other

Comment	(On) indicates momentary position.
---------	------------------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #2007637-7
SFP+ assy 2x2 spring Fingers Outer Lp Sn



TE Part #1735265-8
1MM FPC HORZ.BOTTOM CONT. ASSY 8P (Au)



TE Part #1969543-8
ASSY, HDR, VERT, BOSSED, DUAL ROW, EP2.5



TE Part #2-1969584-8
ASSY,HDR,VERT,GWT,NO-BOSS, DUAL ROW,EP2.5




TE Part #2-1969543-2
ASSY, HDR, VERT, BOSSED, DUAL ROW, EP2.5




TE Part #1-1969543-6
ASSY, HDR, VERT, BOSSED, DUAL ROW, EP2.5



TE Part #1-1969543-4
ASSY, HDR, VERT, BOSSED, DUAL ROW, EP2.5



TE Part #1-1969543-8
ASSY, HDR, VERT, BOSSED, DUAL ROW, EP2.5



TE Part #1977907-1
CAT5e In-Line Shielded Coupler

Documents

Product Drawings

[SUBMIN PUSHBUTTON, PBS9MTRES](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2267130-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267130-3_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267130-3_A.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[Subminiature Switches](#)

English

[Product Environmental Compliance](#)

[Product Compliance](#)

English

[Product Compliance](#)

English