



EU Power Strip with 4 Outlets, 2 USB Charging Ports and Switch

Four German Type F Outlets, Two USB-A Ports with 2.1 A Shared Output, Built-in 2 m Power Cord with Type F Plug, 16 A, On/Off Switch, White

Part No.: [168342](#)

EAN-13: 0766623168342 | UPC: 766623168342

Power Strip with USB Ports and Switch - German type - 4 outlets and 2 USB ports - versatile power solution for home and office

Plug your printer, PC, router, TV or other home/office electronics into this 4-way power strip from Manhattan. It is compatible with standard electrical equipment and features four German Type F outlets in a durable white plastic housing for a clean look. This strip also lets you save your wall charger for another device somewhere else. You can connect your devices right to the USB-A ports and charge them with shared output power up to 2.1 A. This 4-outlet Power Strip is ideal for charging any combination of mobile devices such as tablets, headphones and more. The illuminated on/off switch provides one-touch control over all connected devices.

Features:

- Four-way power strip for standard electrical equipment, ideal for home and office use
- Two USB-A ports delivering up to 2.1 A shared power to charge phones, tablets or other USB-A powered devices
- Built-in 2 m power cord with German Type F plug
- Illuminated two-pole on/off safety switch
- Sockets with increased touch protection through contact shutters

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

- Housing with IP20-rated protection
- Right-angled outlet orientation
- Durable plastic housing
- For indoor use only
- Three-year warranty

Specifications:

Standards and Certifications

- CE
- RoHS

Electrical

- AC input: 220.0 - 250.0 V; 50 - 60 Hz
- Operating voltage: 230.0 V
- Socket/outlet standard: German Type F; IEC60884
- Plug standard: German Type F; IEC60884
- Maximum load: 3680.0 W
- Load current: 16.0 A
- Two USB-A charging ports: 2.1 A / 5.0 V DC total output power (shared)

Physical

- Dimensions (L x W x H): 274 x 50 x 42 mm
- Cable length: 2 m
- Cable type: H05VV-F 3G 1.5 mm²
- Net weight: 420 g
- Gross weight: 430 g
- Housing: plastic

Operating Environment

- Operation temperature: 0 - 35°C
- Storage temperature: -10 - 50°C
- Humidity (noncondensing): 10 - 80%

Package Contents

- EU Power Strip with 4 Outlets, 2 USB Charging Ports and Switch

This product is part of a group; the complete list of variations follows:

- #167802 - 4-Way
- #168342 - 4-Way with 2 USB Charging Ports and On/Off Switch
- #168304 - 6-Way
- #168335 - 6-Way with On/Off Switch
- #168311 - 6-Way with On/Off Switch and Surge Protector

