
Data sheet

Article Description

Article image

LED Line Intermediate Dimmer Type 8130

- **programmable brightness**
- **memory function**
- **soft-Start**
- **internal strain relief**



Suitable for: dimmable LED lamps,
HV-halogen lamps,
incandescent lamps,
LV-halogen lamps

Rated voltage: 230 V ~ (+/- 10 %), 50 Hz,

Rated power: 100 W/VA, LED 1-66W

Operating principle: trailing-edge

Dimensions: L/B/H 52 x 100 x 19 mm

Function: on/off via push-button switch,
dimming via push-button switch

Cable: 2-wire cable HV03VV 2*0,75 mm² without protective conductor

Connection: screw terminals 0.75 mm² (flexible)

Safety class: IP20



inter BÄR No.	Version
8130-004.01	black without cable
8130-008.01	white without cable
8130-204.01	black with 1.2 m power cable + 0.3 m lamp cable
8130-208.01	white with 1.2 m power cable + 0.3 m lamp cable

Technical modifications reserved!!!
Works at 230V-mains must only be carried out by a specialist!!!