

TOSHIBA



55UA3D63DG

UA3D Series

UA3D Series: 4024862127480

- ⊗ Android TV
- ⊗ Google Assistant
- ⊗ Chromecast Built in
- ⊗ 4K UHD HDR
- ⊗ Dolby Vision HDR
- ⊗ Google Play Store

androidtv  Ok Google  Chromecast built-in 

E

64kWh/1000

G

HDR

123kWh/1000

androidtv

Android TV

Explore thousands of movies, shows, games and get answers to your questions on the big screen with Android TV and Google Voice Assistant. Plus, with Chromecast built-in, simply cast movie, shows and photos from all your family's devices.



Google Assistant

Use your voice to search for shows, control your TV, plan your day, and more. Just ask Google.



Chromecast built in

Stream the entertainment you love from your phone, tablet or laptop to your TV.



4K UHD HDR

Awarded the 4K HDR Ultra HD logo, all our 4K HDR TVs have been proven to deliver and faithfully display 4K HDR content in all its glory.



DISPLAY

| | |
|-------------------------|--------------------------|
| Screen Size (inch / cm) | 55" / 139cm |
| Panel Type | Direct Back Light (DLED) |
| Resolution | Ultra HD (3840 x 2160) |
| Brightness | 350 |

SMART TV FEATURES

| | |
|---------------------------|------------|
| HBBTV ver 2.0.2 | Yes |
| Audio-Video Sharing (AVS) | No |
| Smart Portal | Android TV |
| Toshiba TV Smart Center | No |
| Web Browser | No |
| Netflix | Yes |
| YouTube™ | Yes |
| Bluetooth | Yes |
| Screen Mirroring | Chromecast |
| Prime Video | Yes |
| Google Assistant | No |
| Amazon Alexa | No |

ACCESSORIES

| | |
|------------------------|--------------------|
| Remote Control | Yes |
| Remote Control Battery | (AAA) x 2 Alkaline |
| Quick Start Guide | Yes |
| Small Remote Control | No |

FEATURES

| | |
|--------------------------------|---------------|
| HDMI™ ARC | Through HDMI2 |
| USB Recording (PVR Ready) | Yes |
| Channel List USB Cloning | No |
| Teletext | Yes |
| HDMI™ CEC | Yes |
| Basic Hotel Mode | No |
| Media Player | Yes |
| MHL via HDMI™ (Mobile HD Link) | No |
| Child Lock | No |
| NTSC Playback | No |

VIDEO

| | |
|-------------------|---|
| Wide Color Gamut | No |
| HDR | Yes |
| Picture Modes | User, Standard, Vivid, Sport, Movie, Game |
| Dolby Vision HDR | Yes |
| TRU Flow | Yes |
| TRU Resolution | Yes |
| TRU Micro Dimming | Yes |

TUNER / BROADCASTING

| | |
|---|----------------|
| HEVC (H.265) Decoder | Yes |
| Tuner Type | HD DVB-T2/C/S2 |
| UHD from Satellite | Yes |
| Dual Tuner | No |
| Electronic Program Guide (EPG) | Yes |
| Auto Search | Yes |
| Program Storage Capacity (Analog) | 200 |
| Program Storage Capacity (Digital S/S2) | 10000 |
| Program Storage Capacity (Digital T/T2/C) | 800 |

POWER / ENERGY

| | |
|---------------------------------------|-------------|
| Energy Class | E |
| Energy Consumption(kWh/1000h) | 64kW/1000h |
| Energy Class(HDR) | G |
| Energy Consumption(kWh/1000h)(HDR) | 123kW/1000h |
| Stand-By Energy Consumption (Average) | <0.5W |
| Working Voltage - Frequency | 220-240V AC |
| 12V TV (Mobile TV) | No |

CONNECTIONS

| | |
|--------------------------|--------|
| CI+ | Yes |
| HDMI™ | 3 HDMI |
| USB | 2 USB |
| Component (YPbPr) in | No |
| Composite Video/Audio in | No |
| Scart | No |
| Ethernet | Yes |
| Headphone Out | Yes |
| Antenna Input | Yes |
| VGA (PC in - D-Sub15) | No |

MAIN FEATURES

| | |
|-----------------------|-----------|
| Processor Type | Quad Core |
| TV-DVD Combi | No |
| Smart TV | Yes |
| Total Picture Quality | 2100 |
| TRU Picture Engine | Yes |

MECHANICAL

| | |
|-------------------------------|------------------|
| Boxed dimensions (mm) | 1369 x 154 x 860 |
| Dimensions with stand (mm) | 1243 x 249 x 755 |
| Dimensions without Stand (mm) | 1243 x 81 x 720 |
| Gross Weight (kg) | 21 |
| Net Weight (kg) | 16 |
| VESA (Wall mount) WxH | 200mm x 200mm |

SOUND

| | |
|--------------------------|---------------------------|
| Dolby Audio™ | Yes |
| Audio Output Power (RMS) | 2x10W |
| Speaker Type | Down Firing |
| Internal Subwoofer | No |
| Sound Modes | Smart, Movie, Music, News |
| DTS | Yes |
| Equalizer | 5 band |
| Onkyo | Sound by Onkyo |

Toshiba is a registered trademark of Toshiba Corporation and its used by Vestel or its subsidiary for products described here in under license from Toshiba Visual Solutions Corporation. All other product and brand names are trademarks or registered trademarks of their respective companies. Design, features and specifications are subject to change without notice. Non-metric weights and measurements are approximate. Screen images are simulated.