



LogiLink®

USB-C™ 20 W Wall Charger

Art. No.: PA0278



Smaller yet More Powerful

Rapidly charge your devices with 20 W USB-C Power Delivery; it is compact and lightweight for easy portability and storage. Keep your devices charged at home, in the office, or on-the-go.



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



20 W output for a variety of devices from tablets to smartphones; it powers your devices at incredible speeds.



Supports PPS (Programmable Power Supply) charging and adjusting the output power in real-time, depending on device's charging status, feeding it with maximum power.



Extremely safe as it comes with overcurrent, overvoltage, overheating and short circuit protections.



Compact size makes it lightweight and easily fits into your laptop bag or backpack. The perfect mobile accessory for traveling.




Widely compatible with most USB-C devices such as smartphones, tablets and much more.



Specification:

Input	230 V AC 50/60 Hz 0,6 A
Output	5 V/3 A (15 W), 9 V/2,22 A (19,98 W), 12 V/1,67 A (20 W) PPS: 3,3–11 V/1,8 A Max. total output: 20 W
Auto Power Adjustment	Yes
Efficiency	Level VI
Operating Temperature	-10–35 °C
Storage Temperature	-20–80 °C
Relative Humidity	35–85% (non-condensing)
Storage Humidity	5–95% (non-condensing)
Color	White
Dimensions	3 x 3 x 3,06 cm (without plug) 3 x 3,55 x 6,8 cm (with plug)
Weight	43 g



Package Contents:

- » 1x USB-C Wall Charger
- » 1x User Manual

Package Information:

- » Packing Dimension: 120 x 75 x 40 mm
- » Packing Weight: 0,065 kg
- » Carton Dimension: 420 x 320 x 140 mm
- » Carton Q'ty: 40 pcs
- » Carton Weight: 2,6 kg



⚠ Proper use of the PD function can only be guaranteed in combination with certified USB cables with E-Mark chipset.

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



PA0278



Made in China