

Datasheet

01.02.2023



Part n°	204701
Product name	ekey sLine fingerprint set SC Gira 106 V4A
Product name 2	ekey sLine fingerprint sca. set black Gira 106 V4A
EAN code	9120068258111
Customs tariff number	8471 9000
Origin country	AT
Weight:	0.7 kg
Application area	Use in domestic and business applications

The ekey sLine fingerprint scanner set for door stations is a biometric access solution that grants keyless access to buildings using intuitive touch operation. The set includes the door station module with integrated ekey sLine fingerprint scanner and the ekey control unit DRM with two relays. The system is administered via the ekey bionyx app.

Technical data

Operational data	
Supply typ:	DC
Maximum supply voltage:	30 V
Minimum supply voltage:	10 V
Supply voltage rating:	24 V
Maximum current consumption:	17 mA
Minimum current consumption:	14 mA
Current consumption rating:	16 mA
Maximum power:	0.4 W
Minimum power:	0.3 W
Power rating:	0.4 W
Minimum operating temperature:	-25 °C
Maximum operating temperature:	70 °C
Maximum humidity:	90 %rel
IP code:	IP54
Suitable for unprotected outdoor area:	yes
Suitable for protected outdoor area:	yes
FAR:	1:10 000 000
FRR:	1:100
Tolerance rated voltage:	0.1
Signaling:	Visual Acoustic

Mechanical data	
Minimum mounting height:	105 cm
Width:	106 mm
Length/height:	106 mm
Depth:	32 mm
Material:	stainless steel V4A
Surface:	Stainless steel
UV-resistant:	yes

Communication Bluetooth	
Bluetooth standard:	4.2
Bluetooth class:	Class 1
Maximum Bluetooth range:	100 m
Typical Bluetooth Range:	10 m