

KERN CDS 15K0.05

KERN

Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications



Maximum creep (30 minutes)	1 g
Default unit	kg

Display	
Display type	LCD
Display type	7 segment LED
Display backlight	✓
Display screen size	89×30 mm
Display segments	7
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	225×115×60 mm
Dimension display device (W×D×H)	225×115×60 mm
Dimensions weighing surface (W×D)	308×318 mm
Dimensions weighing surface	308×318 mm
Dimensions weighing platform (W×D×H)	308×318×75 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Material display housing	plastic
Level indicator	✓
Wall mount	✓
Display device cable length	2,5 m

Functions	
PreTare function	✓
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Hook (optional)
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	300.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	50 mg
Smallest piece weight when piece counting - normal conditions	500 mg
Reference quantity	5, 10, 20, 50, n (any number of pieces)

Category	
Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CDS

Measuring System	
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg
Readability [d]	0,00005 kg
Reproducibility	0,0001 kg
Linearity	± 0,00025 kg
Resolution	300.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (F1)
Possible calibration points	2 kg; 5 kg; 10 kg; 15 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,00025 kg
Construction type of the scale	Single-range balance
Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa
Maximum creep (15 minutes)	500 mg

KERN CDS 15K0.05



Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications

Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)
	USB-Device (optional)
	KUP
	WiFi (optional)
compatible with EasyTouch	✓

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	UK
	US
	CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	5,9V, 1A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 13 mm
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	-10 °C
---------------------------	--------

Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkKS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	520×390×150 mm
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	9,8 kg

Product information

GTIN/EAN number	4045761243903
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

