



Discover more details and matching accessories online!

High-resolution precision balance made of stainless steel with IP protection

Features

- High-quality tuning fork weighing system for rapid display of the weight, very precise dispensing and a high level of mechanical robustness
- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- IP65 dust and spray protection (in accordance with EN 60529)
- Level indicator and levelling feet for precise levelling of the scale, fitted as standard
- **1** RS-232 data interface for connection to a printer as standard

Technical data

- Large LCD display, digit height 16,5 mm
- Dimensions weighing surface, stainless steel
 - A** ø 140 mm
 - B** W×D 190×190 mm, see larger picture
- Overall dimensions W×D×H 320×205×90 mm
- Net weight approx. 3,0 kg
- Permissible ambient temperature 10 °C/30 °C

STANDARD



OPTION



Model	Weighing capacity	Readability	Reproducibility	Linearity	Weighing plate	Options
						Calibr. Certificate
	[Max]	[d]				DAkkS accr. KERN
KERN	g	g	g	g		
PWS 800-2	820	0,01	0,01	± 0,01	A	963-127
PWS 3000-1	3200	0,1	0,1	± 0,1	B	963-127
PWS 8000-1	8200	0,1	0,1	± 0,1	B	963-128