

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0781720411

Status:

Active

Overview:

Pico-EZmate and Pico-EZmate Plus Wire-to-Board Connector Systems

Description:

Pico-EZmate Female Crimp Terminal, Gold (Au) over Nickel Plating 0.10µm, 28-30 AWG, Reel



Series image - Reference only

Documents:

- Drawing (PDF)

Application Specification AS-78172-001-001 (PDF)
- Product Specification 781720000-PS-000 (PDF)

Application Specification AS-78172-006-001 (PDF)
- Product Specification 781720002-000 (PDF)

Packaging Specification SPK-78172-003-001 (PDF)
- Product Specification 781721000-PS-000 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	78172
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Pico-EZmate and Pico-EZmate Plus Wire-to-Board Connector Systems
Product Name	Pico-EZmate
Taxonomy	Crimp Terminals
UPC	800756842936

Physical

Durability (mating cycles max)	10
Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	5.440/mg
Packaging Type	Reel
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.60-0.70mm
Wire Size AWG	28, 30
Wire Size mm²	0.055-0.089

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-78172-001-001, AS-78172-006-001
Crimp Specification	781720013-C00
Packaging Specification	SPK-78172-003-001
Product Specification	781720000-PS-000, 781720002-000, 781721000-PS-000
Sales Drawing	781720400-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

78172 Series

Use With

Receptacle Housing 78172

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FA2 Mechanical Feed Crimp Applicator for 1.20mm Pitch Pico-EZmate Crimp Terminals, 28-30 AWG	2130694700
Hand Crimp Tool for 1.20mm Pitch Pico-EZmate Crimp	2133096500

Terminals, 28-30 AWG Extraction and Activation Tool	<u>638132700</u>
T2 Terminator for 1.20mm (.047") Pitch Pico-EZmate Wire-to-Board Crimp Terminal	<u>639125900</u>

Japan	
Description	Product #
S-1 Applicator for Pico-EZmate Receptacle Terminals, 28-30 AWG	<u>5780593700</u>

This document was generated on 11/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION