

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5047543120

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.30mm Pitch Easy-On Back Flip FPC Connector, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 31 Circuits



Series image - Reference only

Documents:

[3D Model \(PDF\)](#)

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-504754-002-001 \(PDF\)](#)

[Application Specification AS-504754-002-001 \(PDF\)](#)

[Packaging Specification 5047549200-200 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Overview

Product Name

Taxonomy

UPC

FFC/FPC Connectors

504754

Easy-On FFC FPC Connectors

Easy-On

FFC / FPC Connectors

887191596648

Physical

Actuator Type

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Contact Position

Durability (mating cycles max)

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to PCB

Stackable

Temperature Range - Operating

Wire/Cable Type

Back Flip

31

31

Black

Dual

10

0.75mm

Copper Alloy

Gold

Gold

Liquid Crystal Polymer

39.531/mg

1

Right Angle

No

Surface Mount

None

Embossed Tape on Reel

0.30mm

0.30mm

Yes

No

-40° to +105°C

FPC only

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.3A

50V

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

AS-504754-002-001

5047549200-200

PS-504754-002-001

SD-504754-003-001, SD-504754-004-001

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

504754 Series

This document was generated on 01/20/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION