

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0357460110

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Female Crimp Terminal, 20-22 AWG, Type A



Documents:	
Drawing (PDF)	Application Specification 351500000ASENG-000 (PDF)
3D Model	Application Specification 351500000ASKOR-000 (PDF)
3D Model (PDF)	Packaging Specification PK-35746-001-001 (PDF)
Product Specification 351800400-001 (PDF)	Datasheet (PDF)
Product Specification 351800600-001 (PDF)	Brochure (PDF)
Product Specification PS-35150-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-35182-003-001 (PDF)	

General	
Product Family	Crimp Terminals
Series	35746
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
Taxonomy	Crimp Terminals
UPC	800753856417
Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.293/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.60mm max.
Wire Size AWG	20, 22
Wire Size mm²	0.30-0.50
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Crimp Specification	CS-35745-001-001, CS-35745-001-002
Packaging Specification	PK-35746-001-001
Product Specification	351800400-001, 351800600-001, PS-35150-001-001, PS-35182-003-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

35746 Series

Use With

VersaBlade Standard Receptacle Housings
[351500300](#) , [351500304](#) , [351500309](#) ,
[351500310](#) , [351500314](#) , [351500319](#) ,
[351503309](#) , [351503319](#) , [351504319](#) ,
[351500400](#) , [351500404](#) , [351500409](#) ,
[351500410](#) , [351500412](#) , [351500414](#) ,
[351500419](#) , [351503419](#) , [351504419](#) ,
[351500600](#) , [351500604](#) , [351500609](#) ,
[351500610](#) , [351500612](#) , [351500614](#) ,
[351500619](#) , [351503609](#) , [351503619](#) ,
[351504619](#)
VersaBlade Standard
Plug Housings [35151](#)
VersaBlade
Multi-Module Receptacle Housings [35180](#)
 , [35524](#) , [2026500909](#) , [2041020609](#) ,
[2041020429](#)
 VersaBlade Multi-Module
Plug Housings [351810200](#) , [351810204](#)
 , [359650200](#) , [359650204](#) , [359650210](#)
 , [359650214](#) , [359659200](#) , [359659203](#) ,
[2041020209](#) , [2041020219](#) , [2041020409](#) ,
[2041020419](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	638132700
Hand Crimp Tool for Industry standard 1.78mm Terminals	638196800
T2 Terminator Die	638529000
FineAdjust Applicator	638629000
FineAdjust Applicator for VersaBlade .070 Male and Female Terminals, 20-22 AWG	639042200

This document was generated on 01/25/2023
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION