

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0903270361](#)
Status: **Active**
Overview: [Picoflex Ribbon-Cable Connectors](#)
Description: Picoflex PF-50, Low Profile, IDT Receptacle, 8 Circuits, White, Tin (Sn) Plated, Reeling Option C

Documents:

3D Model	Application Specification 908140000-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-90327-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-99020-0011-001 (PDF)	

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	Ribbon Cable / Wire Trap Connectors
Series	90327
Comments	Low Profile, Reeling Option C
Component Type	Housing
Gender	Receptacle
Glow-Wire Capable	No
Overview	Picoflex Ribbon-Cable Connectors
Product Name	Picoflex
Taxonomy	Connector Housings
UPC	800753673250

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	White
Durability (mating cycles max)	30
Entry Angle	Vertical
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.510/g
Number of Rows	2
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	IDT or Pierce
Wire Insulation Diameter	1.00mm max.
Wire Size AWG	26, 28
Wire/Cable Type	Ribbon Cable



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90327 Series](#)

Mates With

Low Profile Vertical [90325](#) , Low Profile
Right Angle [90800](#) , [90715](#) , [90814](#) , [90779](#)
Vertical, [91714](#) 1.27mm Pitch Picoflex PF-50
Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for Connectors	621006000
-------------------------------	---------------------------

Extraction Tool for Picoflex PF-50 Connectors, 4-26 Circuits	690081070
--	---------------------------

Electrical

Current - Maximum per Contact
Voltage - Maximum

1.2A
250V

Material Info**Reference - Drawing Numbers**

Application Specification
Packaging Specification
Product Specification
Sales Drawing

908140000-AS-000
PK-90327-001-001
PS-99020-0011-001
SDA-90327-001

Semi-Automatic Bench Press PB14
for 4-26 Circuit
Semi-Automatic PB14 Bench Press
with Auto De-reeling
Assembly of De-Tape Unit for
PB14 Part Number
691271001

691271001
691271004
691275045

This document was generated on 01/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION