

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2005290090

Status:

Active

Overview:

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, 1.90mm Height, Single Bottom Contact (FS19), Right-Angle, Surface Mount, ZIF, 9 Circuits

General

Product Family

FFC/FPC Connectors

Series

200529

Comments

Black Actuator

Overview

easyon_ffc_fpc_connectors

Product Name

Easy-On

Taxonomy

FFC / FPC Connectors

UPC

889056681889

Physical

Actuator Type

Front Flip

Circuits (Loaded)

9

Circuits (maximum)

9

Color - Resin

Beige

Contact Position

Bottom

Durability (mating cycles max)

25

Mated Height

1.90mm

Material - Metal

Phosphor Bronze

Material - Plating Mating

Tin-Silver-Bismuth

Material - Plating Termination

Tin-Silver-Bismuth

Material - Resin

Liquid Crystal Polymer

Net Weight

132.442/mg

Number of Rows

1

Orientation

Right Angle

PCB Locator

No

PCB Mounting

Surface Mount

PCB Retention

Yes

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

1.00mm

Pitch - Termination Interface

1.00mm

Plating min - Mating

1.016µm

Plating min - Termination

1.016µm

Polarized to PCB

Yes

Stackable

No

Temperature Range - Operating

-40° to +85°C

Wire/Cable Type

FFC/FPC

Electrical

Current - Maximum per Contact

1.0A

Voltage - Maximum

125V

Material Info

Reference - Drawing Numbers

Packaging Specification

2005299200-200

Product Specification

2005290000-000

Sales Drawing

2005290000-000, 2005290006-000, 2005291000-000, 2005291006-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

200529 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION