

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0357480310

Status:

Active

Overview:


VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Female Crimp Terminal, 18+18, 20+20 AWG, Type B

Documents:	
Drawing (PDF)	Application Specification 351500000ASENG-000 (PDF)
Product Specification 351800400-001 (PDF)	Application Specification 351500000ASKOR-000 (PDF)
Product Specification 351800600-001 (PDF)	Packaging Specification PK-35748-003-001 (PDF)
Product Specification PS-35150-001-001 (PDF)	Datasheet (PDF)
Product Specification PS-35150-003-001 (PDF)	Brochure (PDF)
Product Specification PS-35182-003-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	35748
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
Taxonomy	Crimp Terminals
UPC	800754249874
Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.333/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.8mm + 2.8mm max.
Wire Size AWG	18+18, 20+20
Wire Size mm²	2(0.50-0.85)
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Crimp Specification	CS-35745-001-001, CS-35745-001-002
Packaging Specification	PK-35748-003-001
Product Specification	351800400-001, 351800600-001, PS-35150-001-001, PS-35150-003-001, PS-35182-003-001
Sales Drawing	SD-35748-003-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

35748 Series

Use With

VersaBlade Standard Receptacle Housings [351500400](#) , [351500404](#) , [351500409](#) , [351500410](#) , [351500412](#) , [351500414](#) , [351500419](#) , [351503419](#) , [351504419](#) , [351510310](#) , [351510314](#) , [351510319](#) , [351513319](#) , [351514319](#)
 VersaBlade Standard Plug Housings [351510410](#) , [351510412](#) , [351510414](#) , [351510419](#) , [351513419](#) , [351514419](#) , [351510610](#) , [351510612](#) , [351510614](#) , [351510619](#) , [351513619](#) , [351514619](#)
VersaBlade Multi-Module Receptacle Housings [351800400](#) , [351800404](#) , [351800409](#) , [351803409](#) , [351804409](#) , [2041020429](#)
VersaBlade Multi-Module Plug Housings [351810220](#) , [359650220](#) , [359650224](#) , [359659220](#) , [359659223](#) , [359659224](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	638132700
Hand Crimp Tool for 1.80mm-Wide Crimp Terminals	638190700
T2 Terminator Die	638529200
FineAdjust Applicator	638629200
FineAdjust Applicator for VersaBlade .070 Male and Female Terminals, 20+20AWG, 20+18 AWG and 18+18 AWG	639044000

This document was generated on 01/25/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION