

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0541323233

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 32 Circuits, Tin-Silver-Bismuth Plating



Series image - Reference only

Documents:

- [3D Model \(PDF\)](#)[Drawing \(PDF\)](#)[3D Model](#)[2D Drawing \(DXF\)](#)[2D Drawing DXF \(PDF\)](#)[Product Specification PS-54132-062-001 \(PDF\)](#)
- [Packaging Specification SPK-54132-001-001 \(PDF\)](#)[Datasheet \(PDF\)](#)[Product Guide \(PDF\)](#)[RoHS Certificate of Compliance \(PDF\)](#)[Reference Guide \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

Series Name

Taxonomy

UPC

FFC/FPC Connectors

54132

Easy-On FFC FPC Connectors

Easy-On

Slider

FFC / FPC Connectors

887191270623

Physical

Actuator Type

Circuits (Loaded)

Color - Resin

Contact Position

Durability (mating cycles max)

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire/Cable Type

Slider

32

Black, Natural

Bottom

20

94V-0

2.00mm

Phosphor Bronze

Tin-Silver-Bismuth

Tin-Silver-Bismuth

Nylon

375.000/mg

1

Right Angle

2.00mm

No

Surface Mount

None

Embossed Tape on Reel

0.50mm

0.50mm

Yes

No

N/A

-40° to +85°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

50V

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

54132 Series

Mates With

Premo-Flex FFC Cable [15166](#) , [98266](#) ,
[15266](#) , [15366](#)

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-54132-001-001
Product Specification	PS-54132-062-001
Sales Drawing	541320000-000, 541321000-000

This document was generated on 11/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION