

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5044491507

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Vertical, Surface Mount, 0.10µm Gold Plated, Inner Positive Lock, 15 Circuits, Natural

Documents:	
3D Model (PDF)	Product Specification 5013301000-PS-JAP-002 (PDF)
3D Model	Application Specification 5013300000-AS-000 (PDF)
Drawing (PDF)	Packaging Specification SPK-504449-001-001 (PDF)
Product Specification 5013300000-PS-002 (PDF)	Datasheet (PDF)
Product Specification 5013301000-PS-002 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	504449
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
Taxonomy	PCB Headers and Receptacles
UPC	887191267388

Physical	
Breakaway	No
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	285.400/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Robotic Placement	Vacuum Pick-Up Tape
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.0A



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
504449 Series

Mates With
Pico-Clasp Female Housing 501330

Voltage - Maximum	100V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	5013300000-AS-000
Packaging Specification	SPK-504449-001-001
Product Specification	5013300000-PS-002, 5013301000-PS-002, 5013301000-PS-JAP-002
Sales Drawing	5044490000-SD-000

This document was generated on 01/25/2023
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION