

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0524372433

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 24 Circuits, Tin-Silver-Bismuth Plating



Series image - Reference only

Documents:	
Drawing (PDF)	Product Guide (PDF)
Product Specification PS-52437-028-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification SPK-52437-001-001 (PDF)	Reference Guide (PDF)
Datasheet (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	52437
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
Series Name	Slider
Taxonomy	FFC / FPC Connectors
UPC	887191292991
Physical	
Actuator Type	Slider
Circuits (Loaded)	24
Color - Resin	Natural
Contact Position	Bottom
Durability (mating cycles max)	20
Flammability	94V-0
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Silver-Bismuth
Material - Plating Termination	Tin-Silver-Bismuth
Material - Resin	Nylon
Net Weight	317.720/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52437 Series

Mates With

Premo-Flex FFC Cable [15166](#) , [98266](#) , [15266](#) , [15366](#)

Packaging Specification
Product Specification
Sales Drawing

SPK-52437-001-001
PS-52437-028-001
SD-52437-023-001, SD-52437-024-001

This document was generated on 11/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION