

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5055780871

Status:

Active

Overview:

Micro-Lock Plus Connector System

Description:

2.00mm Pitch, Micro-Lock Plus PCB Header, Single Row, Right-Angle, Surface Mount, Matte Tin Plating, Positive Lock, 8 Circuits, Low-Halogen, Black

- Documents:
- 3D Model

Application Specification 5055700001-A03 (PDF)
- Drawing (PDF)

Packaging Specification 5055789200-200 (PDF)
- 3D Model (PDF)

Datasheet (PDF)
- Product Specification 5055700001-PS-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 5055701001-PS-000 (PDF)

Agency Certification

UL

E29179

General

Product Family

PCB Headers

Series

505578

Application

Signal, Wire-to-Board

Component Type

PCB Header

Overview

Micro-Lock Plus Connector System

Product Name

Micro-Lock Plus

Taxonomy

PCB Headers and Receptacles

UPC

889056580021

Physical

Breakaway

No

Circuits (Loaded)

8

Circuits (maximum)

8

Color - Resin

Black

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Matte Tin

Material - Plating Termination

Matte Tin

Material - Resin

Polyamide

Net Weight

893.040/mg

Number of Rows

1

Orientation

Right Angle

PCB Locator

No

PCB Retention

Yes

Packaging Type

Embossed Tape on Reel

Pitch - Mating Interface

2.00mm

Pitch - Termination Interface

2.00mm

Plating min - Mating

1.000µm

Plating min - Termination

1.000µm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Stackable

No

Temperature Range - Operating

-40° to +105°C

Termination Interface: Style

Surface Mount



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

505578 Series

Mates With

Micro-Lock Plus Receptacle Housing
505570

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	5055700001-A03
Packaging Specification	5055789200-200
Product Specification	5055700001-PS-000, 5055701001-PS-000
Sales Drawing	5055780001-000

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION