

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0536471274

Status:

Active

Overview:

SlimStack Board-to-Board/Board-to-FPC Connectors

Description:

SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 8.00 or 14.00mm Mated Height, 6.40mm Mated Width, 120 Circuits

Documents:

- [3D Model \(PDF\)](#)[Datasheet \(PDF\)](#)
- [3D Model](#)[Product Guide \(PDF\)](#)
- [Drawing \(PDF\)](#)[RoHS Certificate of Compliance \(PDF\)](#)
- [Product Specification 527600000-000 \(PDF\)](#)[Reference Guide \(PDF\)](#)
- [Packaging Specification SPK-53647-001-001 \(PDF\)](#)

General

Product Family	PCB Headers
Series	53647
Application	Board-to-Board, Signal
Comments	Stacking-Type
Component Type	PCB Header
Overview	SlimStack Board-to-Board/Board-to-FPC Connectors
Product Name	SlimStack
Series Name	0.635, Rigid
Taxonomy	Board-to-Board Connectors
UPC	822348204922

Physical

Breakaway	No
Circuits (Loaded)	120
Circuits (maximum)	120
Color - Resin	Brown
Durability (mating cycles max)	50
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	14.00mm, 8.00mm
Mated Width	6.40mm
Material - Metal	Brass, Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1479.783/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.635mm
Polarized to PCB	Yes
Robotic Placement	Metal Cap
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

53647 Series

Mates With

SlimStack 0.635 Receptacle [52885](#) , [52901](#)

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-53647-001-001
Product Specification	527600000-000
Sales Drawing	SD-53647-002-001, SD-53647-003-001, SD-53647-003-002, SD-53647-003-003

This document was generated on 02/06/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION