

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0536271274

Status:

Active

Overview:

SlimStack Board-to-Board/Board-to-FPC Connectors

Description:

SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 10.00 or 16.00mm Mated Height, 6.40mm Mated Width, 120 Circuits

- Documents:
- 3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification 527600000-000 (PDF)

Packaging Specification SPK-53627-001-001 (PDF)

Datasheet (PDF)

Product Guide (PDF)

RoHS Certificate of Compliance (PDF)

Reference Guide (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Series Name

Taxonomy

UPC

PCB Headers

53627

Board-to-Board, Signal

Stacking-Type

PCB Header

SlimStack Board-to-Board/Board-to-FPC Connectors

SlimStack

0.635, Rigid

Board-to-Board Connectors

822348248049

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Mated Height

Mated Width

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to PCB

Robotic Placement

Shrouded

Temperature Range - Operating

Termination Interface: Style

No

120

120

Brown

50

No

No

No

None

None

10.00mm, 16.00mm

6.40mm

Copper Alloy

Gold

Tin

1853.061/mg

2

Vertical

Yes

Yes

Embossed Tape on Reel

0.635mm

Yes

Metal Cap

Fully

-55° to +105°C

Surface Mount



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

53627 Series

Mates With

SlimStack 0.635 Receptacle [52885](#) , [52901](#)

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-53627-001-001
Product Specification	527600000-000
Sales Drawing	SD-53627-001-001, SD-53627-002-001

This document was generated on 02/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION