

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0529011074

Status:

Active

Overview:

SlimStack Board-to-Board/Board-to-FPC Connectors

Description:

SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Receptacle, 12.00 to 16.00mm Mated Height, 6.40mm Mated Width, 100 Circuits

- Documents:
- 3D Model

Datasheet (PDF)
- 3D Model (PDF)

Product Guide (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 527600000-000 (PDF)

Reference Guide (PDF)
- Packaging Specification SPK-52901-001-001 (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Receptacles
Series	52901
Application	Board-to-Board, Signal
Comments	Stacking-Type
Overview	SlimStack Board-to-Board/Board-to-FPC Connectors
Product Name	SlimStack
Series Name	0.635, Rigid
Taxonomy	Board-to-Board Connectors
UPC	822348176595
Physical	
Circuits (Loaded)	100
Circuits (maximum)	100
Color - Resin	White
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Mated Height	12.00mm, 13.00mm, 14.00mm, 15.00mm, 16.00mm
Mated Width	6.40mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2265.465/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.635mm
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	100V



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52901 Series

Mates With

SlimStack 0.635 Plug [55091](#) , [53625](#) , [53647](#) , [53649](#) , [53627](#)

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-52901-001-001
Product Specification	527600000-000
Sales Drawing	SD-52901-008-001, SD-52901-009-001, SD-52901-015-001, SD-52901-017-001

This document was generated on 12/05/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION