

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0587231010

Status:

Active

Overview:

HMC Heavy Duty Rectangular Connectors

Description:

HMC Rectangular Industrial Hood, Multi-Module Type, Right-Angle, External Thread, 48-72 Circuits



Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-58719-005-001 (PDF)

Product Specification PS-58719-006-001 (PDF)

Application Specification AS-58723-004-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	I/O Connectors
Series	58723
Application	Panel-Mount
Component Type	Hood
Overview	HMC Heavy Duty Rectangular Connectors
Product Name	HMC
Taxonomy	I/O Connectors
Type	N/A
UPC	756054376119
Physical	
Circuits (Loaded)	48
Circuits (maximum)	48
Durability (mating cycles max)	50
Lock to Mating Part	Yes
Material - Metal	Stainless Steel
Material - Plating Mating	N/A
Net Weight	373181.700/mg
Orientation	Right Angle
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	N/A
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP65
Electrical	
Current - Maximum per Contact	13.0A, 20.0A
Voltage - Maximum	300V DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-58723-004-001
Product Specification	PS-58719-005-001, PS-58719-006-001
Sales Drawing	SD-58723-006-001, SD-58723-006-002

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(a)-I,6(b)-II	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

58723 Series

Mates With

587190010 Panel Mount Bracket Type A Polarization, 587190020 PanelMount Bracket Type B Polarization

Use With

58866 End Bell Cap Assembly, 58721 Hood Bracket

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION