

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015445864

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Receptacle, Through Hole, Dual Row, High Profile, Vertical, High-Temperature, 64 Circuits

Documents:

- Drawing (PDF)

Application Specification 713080001-AS-000 (PDF)
- 3D Model

Packaging Specification PK-70873-0660-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-70181-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

71850

Application

Board-to-Board, Signal

Component Type

PCB Receptacle

Overview

C-Grid Connector Products

Product Name

C-Grid

Taxonomy

PCB Headers and Receptacles

UPC

800753604148

Physical

Circuits (Loaded)

64

Circuits (maximum)

64

Color - Resin

Black

Durability (mating cycles max)

50

Flammability

94V-0

Glow-Wire Capable

No

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

5.386/g

Number of Rows

2

Orientation

Vertical

PC Tail Length

3.05mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.57mm

Packaging Type

Tray

Pitch - Mating Interface

2.54mm

Plating min - Mating

0.381µm

Plating min - Termination

1.905µm

Polarized to PCB

No

Temperature Range - Operating

-40° to +105°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

2.5A

Voltage - Maximum

250V

Solder Process Data

Lead-freeProcess Capability

SMC&WAVE



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

71850 Series

Mates With

C-Grid Vertical Header [70246](#) , [70567](#) ,
[70568](#) . C-Grid Right-Angle Header [70247](#) ,
[74162](#) . C-Grid Vertical Breakaway Header
[70280](#) , [71308](#) , [70287](#) . C-Grid Right-Angle
Breakaway Header [71764](#) , [70216](#)

Process Temperature max. C	260
Material Info	
Engineering Number	71850-0159
Reference - Drawing Numbers	
Application Specification	713080001-AS-000
Packaging Specification	PK-70873-0660-001
Product Specification	PS-70181-001
Sales Drawing	SDA-71850-0XXX-001

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION