

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0745480108](#)  
**Status:** **Active**  
**Overview:**  
**Description:** External iPass Mini Multi-Lane SAS Guide Frame for PCI/PCIe Add-In Cards, 1-by-2 Port Size, 1° Cage Angle, Port Keying 4

**General**

Product Family	EMI Cages
Series	<a href="#">74548</a>
Application	Module-to-Board
Comments	Port Keying 4
Component Type	Guide Frame
Overview	ipass
Product Name	Mini-SAS
Taxonomy	High-Speed Pluggable EMI Cages
UPC	822350128926

**Physical**

EMI Panel / Bezel Mount	Behind the Bezel
Light Pipes per Port	0
Material - Metal	Zinc Die Cast
Net Weight	20.932/g
Orientation	Horizontal
Packaging Type	Tray
Port Configuration	1x2
Rear Legs	0
Termination Interface: Style	N/A
Thermal Height	N/A
Thermal Solutions	Closed Top

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-74548-001-001
Sales Drawing	745480100-ASY

**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[74548](#) Series

**Mates With**

[74547](#) iPass Cable Assembly

**Use With**

[75586](#) Receptacle