

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2162911043

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

Standard .093" Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, Tin (Sn) Plating, 4 Circuits, Natural



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	216291
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Standard 093"-to-Pigtail
Overmolded	No
Overview	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
Taxonomy	Power and Signal Cable Assembl
Type	Discrete Wire Assembly
UPC	193264735655
Physical	
Cable Length	600.00mm
Circuits (Loaded)	4
Color - Resin	Natural
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	78.047/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	6.70mm
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size AWG	14
Wire/Cable Type	UL 1015
Electrical	
Current - Maximum per Contact	12.0A
Voltage - Maximum	600V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2162911041-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

216291 Series

Mates With

Standard .093" Plug Housing 19092046 , 19092047 , 19092048 , 19092049 .

Standard .093" Pin and Socket Header 5219

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION