

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2162911061

Status:

Active

Overview:

Description:

Standard .093" Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Dual Row, 150.00mm Length, Tin (Sn) Plating, 6 Circuits, Natural

General

Product Family

Cable Assemblies

Series

216291

Application

Power, Wire-to-Board, Wire-to-Wire

Assembly Configuration

Single Ended Connector

Connector to Connector

Standard 093"-to-Pigtail

Overmolded

No

Overview

standard_093

Product Name

Standard .093"

Taxonomy

Power and Signal Cable Assembl

Type

Discrete Wire Assembly

UPC

193264735662

Physical

Cable Length

150.00mm

Circuits (Loaded)

6

Color - Resin

Natural

Gender

Female-Pigtail

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

36.861/g

Number of Rows

2

Packaging Type

Bag

Pitch - Mating Interface

6.70mm

Plating min - Mating

0.508µm

Plating min - Termination

0.508µm

Single Ended

Yes

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

1.65-4.06mm

Wire Size AWG

14

Wire/Cable Type

UL 1015

Electrical

Current - Maximum per Contact

12.0A

Voltage - Maximum

600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing

2162911061-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

216291 Series

Mates With

Standard .093" Plug Housing [19092066](#)
, [19092067](#) , [19092068](#) , [19092069](#) .
Standard .093" Pin and Socket Header [5219](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION