

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0439141101

Status:

Active

Overview:

Mini-Fit Sr. Power Connectors

Description:

10.00mm Pitch Mini-Fit Sr. Receptacle Housing, Dual Row, 6 Circuits, Black

Documents:	
3D Model	Product Specification TS-42815-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-43914-001-001 (PDF)
3D Model (PDF)	Test Summary TS-42815-004-001 (PDF)
Product Specification PS-42815-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	43914
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.
Taxonomy	Connector Housings
UPC	800753933651

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	10.238/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	10.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	50.0A
-------------------------------	-------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43914-001-001
Product Specification	PS-42815-001-001, TS-42815-001-001
Sales Drawing	SD-43914-002-001
Test Summary	TS-42815-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[43914](#) Series

Mates With

[43915](#) , [43938](#)

Use With

[42815](#) Female Terminal and [43980](#) TPA Clip