

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0440680056

Status:


Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit BMI, 260C Wave Solderable, 4.20mm Pitch, Dual Row, Vertical, for 1.60mm PCB, 4 Circuits, Gold (Au) Plating, with Solderable Retention Clip



|                                                              |                                                                |
|--------------------------------------------------------------|----------------------------------------------------------------|
| Documents:                                                   |                                                                |
| <a href="#">3D Model (PDF)</a>                               | <a href="#">Product Specification PS-45750-001-001 (PDF)</a>   |
| <a href="#">3D Model</a>                                     | <a href="#">Packaging Specification PK-43879-001-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Test Summary TS-43879-001-001 (PDF)</a>            |
| <a href="#">Product Specification PS-43810-001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |

|                                |                                                                                                                                                                                                                                           |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Agency Certification           |                                                                                                                                                                                                                                           |
| CSA                            | LR19980                                                                                                                                                                                                                                   |
| UL                             | E29179                                                                                                                                                                                                                                    |
| General                        |                                                                                                                                                                                                                                           |
| Product Family                 | PCB Headers                                                                                                                                                                                                                               |
| Series                         | 44068                                                                                                                                                                                                                                     |
| Application                    | Board-to-Board, Power, Wire-to-Board                                                                                                                                                                                                      |
| Comments                       | Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus HCS Crimp Terminal Crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current de-rating information. |
| Component Type                 | PCB Header                                                                                                                                                                                                                                |
| Overview                       | <a href="#">Mini-Fit Family Power Connectors</a>                                                                                                                                                                                          |
| Product Name                   | Mini-Fit BMI                                                                                                                                                                                                                              |
| Taxonomy                       | PCB Headers and Receptacles                                                                                                                                                                                                               |
| UPC                            | 800755952438                                                                                                                                                                                                                              |
| Physical                       |                                                                                                                                                                                                                                           |
| Breakaway                      | No                                                                                                                                                                                                                                        |
| Circuits (Loaded)              | 4                                                                                                                                                                                                                                         |
| Circuits (maximum)             | 4                                                                                                                                                                                                                                         |
| Color - Resin                  | Black                                                                                                                                                                                                                                     |
| Durability (mating cycles max) | 30                                                                                                                                                                                                                                        |
| Flammability                   | 94V-0                                                                                                                                                                                                                                     |
| Glow-Wire Capable              | No                                                                                                                                                                                                                                        |
| Material - Metal               | Brass                                                                                                                                                                                                                                     |
| Material - Plating Mating      | Gold                                                                                                                                                                                                                                      |
| Material - Plating Termination | Gold                                                                                                                                                                                                                                      |
| Material - Resin               | High Temperature Thermoplastic                                                                                                                                                                                                            |
| Net Weight                     | 3.157/g                                                                                                                                                                                                                                   |
| Number of Rows                 | 2                                                                                                                                                                                                                                         |
| Orientation                    | Vertical                                                                                                                                                                                                                                  |
| PC Tail Length                 | 4.42mm                                                                                                                                                                                                                                    |
| PCB Locator                    | Yes                                                                                                                                                                                                                                       |
| PCB Retention                  | Yes                                                                                                                                                                                                                                       |
| PCB Thickness - Recommended    | 2.40mm                                                                                                                                                                                                                                    |
| Packaging Type                 | Tray                                                                                                                                                                                                                                      |
| Pitch - Mating Interface       | 4.20mm                                                                                                                                                                                                                                    |
| Pitch - Termination Interface  | 4.20mm                                                                                                                                                                                                                                    |
| Plating min - Mating           | 0.762µm                                                                                                                                                                                                                                   |
| Plating min - Termination      | 0.762µm                                                                                                                                                                                                                                   |
| Polarized to PCB               | Yes                                                                                                                                                                                                                                       |
| Shrouded                       | Partial                                                                                                                                                                                                                                   |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

[44068](#) Series

Mates With

[42385](#) , [42474](#) , [44475](#) , [44516](#) , [5557](#) Dual Row

|                                                |                                    |
|------------------------------------------------|------------------------------------|
| Stackable                                      | No                                 |
| Surface Mount Compatible (SMC)                 | Yes                                |
| Temperature Range - Operating                  | -40° to +105°C                     |
| Termination Interface: Style                   | Through Hole                       |
| <b>Electrical</b>                              |                                    |
| Current - Maximum per Contact                  | 13.0A                              |
| Voltage - Maximum                              | 600V                               |
| <b>Solder Process Data</b>                     |                                    |
| Duration at Max. Process Temperature (seconds) | 005                                |
| Lead-freeProcess Capability                    | WAVE                               |
| Max. Cycles at Max. Process Temperature        | 001                                |
| Process Temperature max. C                     | 260                                |
| <b>Material Info</b>                           |                                    |
| <b>Reference - Drawing Numbers</b>             |                                    |
| Packaging Specification                        | PK-43879-001-000                   |
| Product Specification                          | PS-43810-001-001, PS-45750-001-001 |
| Sales Drawing                                  | SD-44068-031-000                   |
| Test Summary                                   | TS-43879-001-001                   |

This document was generated on 02/07/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**