

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901560154

Status:

Active

Overview:

C-Grid III Interconnects

Description:

2.54mm Pitch C-Grid III Crimp Housing Single Row, 14 Circuits, Black

Documents:

3D Model

Application Specification 901190001-AS-000 (PDF)

Drawing (PDF)

Packaging Specification PK-90156-0001-001 (PDF)

Product Specification PS-99020-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Crimp Housings

Series

90156

Application

Signal, Wire-to-Board

Overview

C-Grid III Interconnects

Product Name

C-Grid III

Taxonomy

Connector Housings

UPC

800753667570

Physical

Breakaway

No

Circuits (maximum)

14

Color - Resin

Black

Gender

Receptacle

Glow-Wire Capable

No

Lock to Mating Part

Yes

Material - Resin

PPO

Net Weight

1.096/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.54mm

Temperature Range - Operating

-55° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification

901190001-AS-000

Packaging Specification

PK-90156-0001-001

Product Specification

PS-99020-0001-001

Sales Drawing

SDA-90156-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

90156 Series

Mates With

C-Grid III Vertical Header 90120 , 90136 . C-Grid III Right-Angle Header 90121

Use With

C-Grid III Crimp Terminal 90119 . C-Grid III Pre-Crimped Lead 797582022 , 797582023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION