

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022552502

Status:

Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Crimp Housing, Dual Row, Version B, Polarized, 50 Circuits, Black

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-70058-001 (PDF)

Product Specification PS-70400-001 (PDF)

Packaging Specification PK-70450-100-001 (PDF)

Test Summary TS-70058-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	70450
Application	Signal, Wire-to-Board
Comments	Version B
Overview	SL Modular Connectors
Product Name	SL
Taxonomy	Connector Housings
UPC	800754397667
Physical	
Breakaway	No
Circuits (maximum)	50
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	4.280/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	No
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	70450-0073
Reference - Drawing Numbers	
Packaging Specification	PK-70450-100-001
Product Specification	PS-70058-001, PS-70400-001
Sales Drawing	SD-70450-0050-0075-001
Test Summary	TS-70058-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

70450 Series

Mates With

C-Grid Right-Angle Header 70229 , 70247 .

C-Grid Vertical Breakaway Header 70280 .

C-Grid Vertical Header 70246

Use With

70058 , 71851