

Electrical		FineAdjust Applicator639021900 for 0.635mm CP Terminals, for 0.22mm², 0.35mm², 0.50mm² Metric Wires
Current - Maximum per Contact	6.0A	
Voltage - Maximum	14V DC	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Reference - Drawing Numbers		
Application Specification	AS-64318-002-001, AS-64318-002-CH-001, AS-64318-002-FR-001, AS-64318-002-SP-001, AS-64319-002-001, AS-64319-002-CH-001, AS-64319-002-FR-001, AS-64319-002-SP-001, AS-64322-001-001, AS-64322-001-CH-001, AS-64322-001-FR-001, AS-98420-001-001, AS-98420-001-CH-001, AS-98420-001-FR-001, AS-98420-001-SP-001, AS-98420-002-001, AS-98420-002-CH-001, AS-98420-002-FR-001, AS-98420-002-SP-001	
Crimp Specification	CS-64322-001-001	
Packaging Specification	PK-98913-001-001	
Product Specification	PS-64319-002-001, PS-64326-001-001	
Sales Drawing	SD-64322-001-000	

This document was generated on 02/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION