

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002092166

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 4549, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 14-20 AWG, Reel Packaged

Documents:

Drawing (PDF)

Product Specification PS-02-09-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	4549
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Standard .093" Pin and Socket Connectors
Packaging Alternative	02092167 (Loose)
Product Name	Standard .093"
Taxonomy	Crimp Terminals
UPC	800753746121
Physical	
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.414/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm²	N/A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

4549-(P909)

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-02-09-001

SD-4549-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

4549 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Standard .093" Pin and Socket Terminals	11030006
Terminator Die	11402001
Extractor Tool for .093 and HCS-125 Product Series	638240200
Mini-Mac Applicator for Standard .093" Pin and Socket Terminals, for 14-20 AWG Wire with	638927100

Insulation Diameter
1.65-4.06mm
Mini-Mac Applicator 638927300
for Standard .093"
Pin and Socket
Terminals, for 14-20
AWG Wire with
Insulation Diameter
1.65-4.06mm

This document was generated on 01/25/2023
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION