

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0357450410

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Male Crimp Terminal, 24 AWG, Type A



Series image - Reference only

- Documents:
- 3D Model (PDF)

Application Specification 351500000ASKOR-000 (PDF)
- Drawing (PDF)

Packaging Specification PK-35745-001-001 (PDF)
- 3D Model

Datasheet (PDF)
- Product Specification 351800400-001 (PDF)

Brochure (PDF)
- Product Specification 351800600-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 351500000ASENG-000 (PDF)

General	
Product Family	Crimp Terminals
Series	35745
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
Taxonomy	Crimp Terminals
UPC	756054339091
Physical	
Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.253/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.45mm max.
Wire Size AWG	24
Wire Size mm²	0.29
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Crimp Specification	CS-35745-002-001
Packaging Specification	PK-35745-001-001
Product Specification	351800400-001, 351800600-001
Sales Drawing	SD-35745-001-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

35745 Series

Use With

VersaBlade Standard Receptacle Housings 35150
VersaBlade Standard Plug Housings 351510310 , 351510314 , 351510319 , 351513319 , 351514319 , 351510410 , 351510412 , 351510414 , 351510419 , 351513419 , 351514419 , 351510610 , 351510612 , 351510614 , 351510619 , 351513619 , 351514619
VersaBlade Multi-Module Receptacle Housings 35180 , 35524 , 2026500909 , 2041020609 , 2041020429
VersaBlade Multi-Module Plug Housings 351810210 , 351810214 , 359659210 , 359659213 , 2041020409 , 2041020419

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	<u>638132700</u>
Hand Crimp Tool for Industry standard 1.78mm Tab Terminals, 24-26 AWG Wire	<u>638196900</u>
FineAdjust Applicator for .070 Male and Female Crimp Terminals, 24 AWG	<u>639044200</u>
T2 Terminator for .070 Female Crimp Terminal	<u>639120700</u>

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION