

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000130](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: [Mini-Fit Male Crimp Terminal, Tin \(Sn\), Phosphor Bronze, 16 AWG, Reel](#)

Documents:

Drawing (PDF)	Product Specification PS-5556-002-001 (PDF)
Product Specification 55560002-PS-CH-000 (PDF)	Application Specification 55560001-AS-000 (PDF)
Product Specification 55560002-PS-ES-000 (PDF)	Packaging Specification 55580001-PK-000 (PDF)
Product Specification 55560002-PS-SK-000 (PDF)	Test Summary 55560010-TS-000 (PDF)
Product Specification 55560008-TS-000 (PDF)	Test Summary TS-5556-002-001 (PDF)
Product Specification PS-5556-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	5558
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	39000131 (Loose)
Product Name	Mini-Fit
Taxonomy	Crimp Terminals
UPC	800753827066

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.125/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Engineering Number	5558-PBS3
--------------------	-----------

Reference - Drawing Numbers

Application Specification	55560001-AS-000
Packaging Specification	55580001-PK-000
Product Specification	55560002-PS-CH-000 , 55560002-PS-ES-000 , 55560002-PS-SK-000 , 55560008-TS-000 , PS-5556-001-001 , PS-5556-002-001
Sales Drawing	SD-5558-XSX-001
Test Summary	55560010-TS-000 , TS-5556-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5558](#) Series

Use With

Mini-Fit Jr. Plug Housing [5559](#)
Mini-Fit
BMI Plug Housing [42475](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for Mini-Fit Jr. Terminals	11030044
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	2002182200
FineAdjust Applicator for Mini-Fit Double Crimp Applications Using Two 20 & 22	2037026200

AWG, 20 & 20 AWG,
or 18 & 22 AWG
Wires
FineAdjust Applicator[639039400](#)
for Insulation OD
2.20-2.45mm, 16
AWG
FineAdjust Applicator[639041400](#)
for Insulation OD
2.60-3.15mm, 16
AWG
FineAdjust Applicator[639041500](#)
for Insulation OD
1.80-2.20mm, 16
AWG

This document was generated on 10/31/2022
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION