

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002092170

Status:

Active

Overview:

Standard .093" Pin and Socket Connectors

Description:

2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Tin (Sn) Plated Brass Contact, 14-18 AWG, Large Insulation Crimp, Reel

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	42138
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Standard .093" Pin and Socket Connectors
Packaging Alternative	02092171 (Loose)
Product Name	Standard .093"
Taxonomy	Crimp Terminals
UPC	800753615441
Physical	
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.425/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size AWG	14, 16, 18
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	42138-(P901)
Reference - Drawing Numbers	
Sales Drawing	SD-42138-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42138 Series

Use With

2629 , 1619 Plug or Receptacle Housing, 1545 Plug or Receptacle Housing, 1396 Plug or Receptacle Housing, 1490 Plug or Receptacle Housing, 1261 Plug or Receptacle Housing, 1292 Plug or Receptacle Housing, 1360 Plug or Rec

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Terminator Die	11402212
Extractor Tool for .093 and HCS-125 Product Series	638240200

Mini-Mac Applicator, [638933000](#)
Double 18 AWG
Wires, One Wire
Max Insulation
4.32mm and One
Max Insulation
2.79mm
Mini-Mac Applicator, [638933100](#)
Insulation O.D.
2.36-4.57mm and 18
AWG SPT-3 Wires
Mini-Mac Applicator, [638933200](#)
Double 18 AWG,
Two Wire with
Insulation Diameter
of 2.36-3.56mm
Mini-Mac Applicator, [638933300](#)
Insulation O.D.
2.36-3.56mm and 18
AWG SPT-3 Wires

This document was generated on 09/27/2022
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION