

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190540118

Status:

Active

Description:

RING INSULKRIMP (B-239-08X)

|                                              |                                                      |
|----------------------------------------------|------------------------------------------------------|
| <b>Documents:</b>                            |                                                      |
| 3D Model                                     | Product Specification PS-19902-011-001 (PDF)         |
| Drawing (PDF)                                | Product Specification PS-19902-013-001 (PDF)         |
| 3D Model (PDF)                               | RoHS Certificate of Compliance (PDF)                 |
| Product Specification PS-19902-009-001 (PDF) |                                                      |
| <b>Agency Certification</b>                  |                                                      |
| CSA                                          | LR18689                                              |
| UL                                           | E32244                                               |
| <b>General</b>                               |                                                      |
| Product Family                               | Ring and Spade Terminals                             |
| Series                                       | 19054                                                |
| Crimp Quality Equipment                      | Yes                                                  |
| Taxonomy                                     | Ring and Spade Terminals                             |
| UPC                                          | 800753055056                                         |
| <b>Physical</b>                              |                                                      |
| Flammability                                 | 94V-0                                                |
| Net Weight                                   | 1.103/g                                              |
| <b>Solder Process Data</b>                   |                                                      |
| Lead-freeProcess Capability                  | N/A                                                  |
| <b>Material Info</b>                         |                                                      |
| Engineering Number                           | B-239-08X                                            |
| <b>Reference - Drawing Numbers</b>           |                                                      |
| Product Specification                        | PS-19902-009-001, PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing                                | 190540072-000                                        |

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19054 Series

**Application Tooling | FAQ**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

| <b>Global</b>                                                                                                                                                                                                  |           |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|
| Description                                                                                                                                                                                                    | Product # |
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) Crimp Head for the AT-200 Pneumatic Hand Tool | 640010100 |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool                                                                                                                   | 640160036 |

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION