
This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0387406108
Status: Active
Overview: Beau Barrier Strips
Description: 11.11mm Pitch Beau PCB Fixed Mount Barrier Terminal Strip, Low Profile, 300V, 8 Circuits



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
3D Model (PDF)
Product Specification PS-38730-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Terminal Blocks
Series	38740
Application	N/A
Component Type	One Piece
Overview	Beau Barrier Strips
Product Name	Fixed Mount Barrier
Taxonomy	Terminal Blocks and Barrier St
Type	Barrier Strip
UPC	800756319582

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Number of Rows	1
Orientation	Horizontal
PC Tail Length	5.50mm
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm
Panel Mount	No
Pitch - Mating Interface	11.11mm
Pitch - Termination Interface	11.11mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +130°C
Wire Size AWG	14, 16, 18, 20, 22
Wire Size mm²	0.50-1.50

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Material Info

Engineering Number	74508

Reference - Drawing Numbers

Product Specification	PS-38730-001-001
Sales Drawing	SD-38740-002-001, SD-38740-002-002

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant

REACH SVHC
Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
38740 Series

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION