

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0747641201

Status:

Active

Overview:

SFP+ and SFP Interconnect Solutions

Description:

QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 30 AWG Cable, Pull-to-Release Plunger Style Latch, 2.0m Length



Documents:

[Drawing \(PDF\)](#)

[Packaging Specification PK-74764-1201-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	74764
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	QSFP+-to-4 SFP+
Overview	SFP+ and SFP Interconnect Solutions
Product Name	QSFP Plus, QSFP+, SFP Plus, SFP+
Taxonomy	High-Speed Pluggable I/O Cable
UPC	884982451551
Physical	
Cable Length	2.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	380.500/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	30
Wire/Cable Type	Twinax
Electrical	
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-74764-1201-001
Sales Drawing	747640001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

74764 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION