

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0747642301

Status:

Active

Overview:

SFP+ and SFP Interconnect Solutions

Description:

QSFP+-to-4 SFP+ Passive Cable Assembly, 10Gbps, 28 AWG Cable, Pull-to-Release Plunger Style Latch, 3.0m Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	74764
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	QSFP+-to-4 SFP+
Overview	SFP+ and SFP Interconnect Solutions
Product Name	QSFP Plus, QSFP+, SFP Plus, SFP+
Taxonomy	High-Speed Pluggable I/O Cable
UPC	884982451599
Physical	
Cable Length	3.0m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	512.600/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Twinax
Electrical	
Impedance	100Ω
Shield Type	Full Shield
Shielded	Yes
Material Info	
Reference - Drawing Numbers	
Sales Drawing	747640001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

74764 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION