

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1110401054

Status:

Active

Overview:

zQSFP+ and QSFP+ Integrated Product Solutions

Description:

QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 0.50m Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Packaging Specification PK-111040-1054-001 (PDF)

Agency Certification	
UL	E72548
General	
Product Family	Cable Assemblies
Series	111040
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP+-to-QSFP+
Overview	zQSFP+ and QSFP+ Integrated Product Solutions
Product Name	QSFP Plus, QSFP+
Taxonomy	High-Speed Pluggable I/O Cable
UPC	883906967512
Physical	
Cable Length	0.50m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	88.700/g
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Wire Size AWG	30
Wire/Cable Type	Round
Electrical	
Impedance	100Ω
Material Info	
Engineering Number	111050-1054
Reference - Drawing Numbers	
Packaging Specification	PK-111040-1054-001
Sales Drawing	1110400001-000

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
111040 Series

Mates With
75586 38 Circuit iPass SMT Connector

Use With
74750 , 74768 , 74769 EMI Cage

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION