

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0731716610

Status:

Active

Overview:

BNC Miniature RF Connectors and Cable Assemblies

Description:

75 Ohms, BNC Jack, Right-Angle, Bulkhead, PCB Through Hole, 12 GHz, with Jam Nut and Washer, 2.01mm Peg Length, Tray



Documents:	
3D Model	3D Model (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	RF/Coax Connectors
Series	73171
Overview	BNC Miniature RF Connectors and Cable Assemblies
Product Name	BNC
Style	PCB
Taxonomy	RF / Coaxial Connectors
Type	Miniature
UPC	889056242493
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	15.219/g
Orientation	Right Angle
PCB Mounting	Through Hole
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
Reverse Polar	No
Electrical	
Frequency	12 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73171-661-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

73171 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION