

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731110078

Status:


Active

Overview:

FCT D-Sub Connectors

Description:

FCT Metal Backshell for D-Sub Connector, Shell Size 3, 45° Angle Cable Outlet, Large Inner Chamber, with Rubber Bushing and Knurled Thumb Screw Lock



Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General	
Product Family	D-Sub Products
Series	173111
Overview	FCT D-Sub Connectors
Product Category	Backshell
Product Name	FCT Products
Taxonomy	D-Sub Backshells
Type	Rugged Metal
UPC	889056487788
Physical	
Cable Diameter	3.00-8.50mm
Material - Backshell	Zinc Die-cast
Material - Bushing	TPE
Material - Screw	Brass
Mounting Style	Knurled Thumb Screw Lock
Net Weight	75.000/g
Orientation	45° Angle
Packaging Type	Carton
Plating - Backshell	Nickel
Shield Type	Solid Metal
Shielded	Yes
Temperature Range - Operating	-35° to +100°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No
Material Info	
Engineering Number	FMK3-K282

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

173111 Series

Use With

FCT D-Sub, Size 3

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION