

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194360411

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

MX150L 4 Circuit Rear Mount Flange Sealed Panel Mount Plug for 10-12 AWG Wire, with Gasket, Black



Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-19432-001-001 (PDF)

Packaging Specification PK-19436-001-001 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	19436
Application	Power, Wire-to-Wire
Comments	Mat Seal Color Yellow, Polarized to Mating Part; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
Taxonomy	Connector Housings
UPC	800756731889
Physical	
Circuits (maximum)	4
Circuits Detail	2x2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	7.62mm
Pitch - Termination Interface	7.62mm
Polarized to Mating Part	No
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	40.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19436-001-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19436-002-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19436 Series

Mates With

19432 Receptacle

Use With

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION