
This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0387206215
Status: Active
Overview: Beau Barrier Strips
Description: 9.53mm Pitch Beau PCB Terminal Strip, with Mounting Ends, 15 Circuits



Series image - Reference only

Documents:

3D Model
3D Model (PDF)
Drawing (PDF)
Product Specification PS-38710-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	38720
Application	N/A
Component Type	One Piece
Overview	Beau Barrier Strips
Product Name	Fixed Mount Barrier
Taxonomy	Terminal Blocks and Barrier St
Type	Barrier Strip
UPC	800756333342
Physical	
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	71.969/g
Number of Rows	1
Orientation	Horizontal
PC Tail Length	4.80mm
PCB Retention	Yes
PCB Thickness - Recommended	3.18mm
Panel Mount	No
Pitch - Mating Interface	9.53mm
Pitch - Termination Interface	9.53mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Shrouded	Dual-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +130°C
Wire Size AWG	14, 16, 18, 20, 22
Wire Size mm²	0.50-1.50
Electrical	
Current - Maximum per Contact	15.0A
Voltage - Maximum	300V
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
38720 Series

Engineering Number	72515

Reference - Drawing Numbers

Product Specification	PS-38710-001-001
Sales Drawing	SD-38720-001-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION