

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0194320002

Status:

Active

Overview:

MX150L Industrial Sealed Connector System

Description:

MX150L 4 Circuit Female Receptacle for 8 AWG Wire, Black



Documents:	
3D Model	Packaging Specification PK-19432-001-001 (PDF)
Drawing (PDF)	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19432-001-001 (PDF)	

Agency Certification	
CSA	LR18689
UL	E152602
General	
Product Family	Crimp Housings
Series	19432
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Red, Polarized to Mating Part; IP67 rated; Conforms to UL 1977; NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (TCS)
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
Taxonomy	Connector Housings
UPC	822350191531
Physical	
Circuits (maximum)	4
Circuits Detail	2x2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Net Weight	19.400/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	40.0A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-19432-001-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19432-002-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19432 Series

Mates With

194330002 Male Plug

Use With

19434 Female Terminals

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION